



### Siemens KNX-Geräte mit Seriennummer (KNX-ID)

Dieses Dokument bietet einen Überblick, welche der Siemens KNX-Produkte über eine KNX-Seriennummer, auch KNX-ID genannt, in Klarschrift und/oder in Barcode-Format auf dem Gerätegehäuse verfügen. Zudem verfügt eine Vielzahl der Geräte über ein beigelegtes bzw. abtrennbares Label, das die KNX-ID ebenfalls in Klarschrift sowie Barcode-Format führt und teilweise die MLFB<sup>i</sup>/ASN<sup>ii</sup>-Nummer angibt. Die nachfolgende Tabelle gibt einen umfassenden Überblick.

Die KNX-ID ermöglicht die Nutzung der Siemens App „**Address by ID**“, was die Inbetriebnahme eines KNX-Systems vereinfacht. Anwender können so die physikalische Adresse von KNX-Geräten programmieren. Das abtrennbare Label kann der Installateur an der entsprechenden Stelle im Gebäude- bzw. Elektroinstallationsplan anbringen, damit der ETS-Experte die physikalische Adresse ohne Drücken der Programmier Taste programmieren kann. Wenn die KNX-ID als Barcode vorhanden ist, ist es möglich diese direkt mit einem Barcodescanner einzulesen.

### Siemens KNX devices with serial number (KNX-ID)

This document provides an overview of which Siemens KNX products come with a KNX serial number, also known as KNX-ID, in plain text and/or barcode format on the device housing. Additionally, many devices come with an attached or detachable label that also displays the KNX-ID in clear text and barcode format, and sometimes includes the MLFB<sup>i</sup>/ASN<sup>ii</sup> number. The comprehensive overview is provided in the table below.

The KNX-ID allows for the use of the Siemens App “**Address by ID**”, which simplifies the commissioning of a KNX system. Users can program the physical address of KNX devices using this app. The detachable label can be attached by the installer at the corresponding location in the building or electrical installation plan, allowing the ETS expert to program the physical address without pressing the programming button. If the KNX-ID is available as a barcode, it can be directly scanned using a barcode reader.

**Produktübersicht/Product overview KNX-ID**

Artikel-Nr. Stock no.	Sales text DE	Sales text EN	Gehäuse Housing		Abtrennbares Label Detachable label		
			KNX ID Klarschrift clear text	KNX ID Barcode	KNX ID Klarschrift clear text	MLFB/ASN Klarschrift clear text	KNX ID Barcode
5WG1141-1AB03	KNX/DALI Gateway plus, 64 DALI EVGs	KNX/DALI Gateway plus, 64 DALI ECGs	✓	✓	✓	✓	✓
5WG1141-1AB14	KNX/DALI Gateway, 64 DALI EVGs	KNX/DALI Gateway, 64 DALI ECGs	✓	✓	✓	✓	✓
5WG1141-1AB21	KNX/DALI Gateway Twin plus, 2x 64 DALI EVGs	KNX/DALI Gateway Twin plus, 2x 64 DALI ECGs	✓	✓	✓	✓	✓
5WG1141-1AB31	KNX/DALI Gateway Twin, 2x 64 DALI EVGs	KNX/DALI Gateway Twin, 2x 64 DALI ECGs	✓	✓	✓	✓	✓
5WG1141-1AB32	KNX/DALI Gateway Twin, 2x 64 DALI EVGs	KNX/DALI Gateway Twin, 2x 64 DALI ECGs	✓	✓	✓	✓	✓
5WG1146-1AB03	KNX IP-Router secure	KNX IP Router secure	✓	✓	✓	✓	✓
5WG1148-1AB23	KNX IP-Schnittstelle secure	KNX IP Interface secure	✓	✓	✓	✓	✓
5WG1201-2DB12	KNX Taster 1-fach, arina, titanweiß	KNX Wall switch, single, arina, titanium white	✓	✓	✓	✓	✓
5WG1201-2DB13	KNX Taster 1-fach, arina, titanweiß LED	KNX Wall switch, single, arina, titanium white, LED	✓	✓	✓	✓	✓
5WG1201-2DB23	KNX Taster 1-fach, arina, schwarz, LED	KNX Wall switch, single, arina, black, LED	✓	✓	✓	✓	✓
5WG1201-2DB43	KNX Taster 1-fach, arina, ash gold, LED	KNX Wall switch, single, arina, ash gold, LED	✓	✓	✓	✓	✓
5WG1202-2DB12	KNX Taster 2-fach, arina, titanweiß	KNX Wall switch, double, arina, titanium white	✓	✓	✓	✓	✓
5WG1202-2DB13	KNX Taster 2-fach arina, titanweiß, LED	KNX Wall switch, double, arina, titanium white, LED	✓	✓	✓	✓	✓
5WG1202-2DB23	KNX Taster 2-fach, arina, schwarz, LED	KNX Wall switch, double, arina, black, LED	✓	✓	✓	✓	✓
5WG1202-2DB43	KNX Taster 2-fach, arina, ash gold, LED	KNX Wall switch, double, arina, ash gold, LED	✓	✓	✓	✓	✓
5WG1203-2DB12	KNX Taster 4-fach, arina, titanweiß	KNX Wall switch, quadruple, arina, titanium white	✓	✓	✓	✓	✓
5WG1203-2DB13	KNX Taster 4-fach, arina, titanweiß, LED	KNX Wall switch, quadruple, arina, titanium white, LED	✓	✓	✓	✓	✓
5WG1203-2DB14	KNX Taster 4-fach, arina, titanweiß, LED	KNX Wall switch, quadruple, arina, titanium white, LED	✓	✓	✓	✓	✓
5WG1203-2DB23	KNX Taster 4-fach, arina, schwarz, LED	KNX Wall switch, quadruple, LED, arina, black	✓	✓	✓	✓	✓
5WG1203-2DB43	KNX Taster 4-fach, arina, ash gold, LED	KNX Wall switch, quadruple, arina, ash gold, LED	✓	✓	✓	✓	✓
5WG1205-2AB12	KNX Touch Control TC5, 5' Touchpanel, weiß	KNX Touch control TC5, 5' Touch panel, white	✓	✓	✓	✗	✓
5WG1205-2AB22	KNX Touch Control TC5, 5' Touchpanel, schwarz	KNX Touch control TC5, 5' Touch panel, black	✓	✓	✓	✗	✓
5WG1220-2AB21	KNX Tasterschnittstelle, 2-fach	KNX Pushbutton interface, 2-fold	✓	✓	✓	✓	✓
5WG1220-2DB31	KNX Tasterschnittstelle, 4-fach	KNX Pushbutton interface, 4-fold	✓	✓	✓	✓	✓
5WG1221-2DB12	KNX Taster 1-fach, i-system, titanweiß	KNX Wall switch, single, i-system, titanium white	✓	✓	✓	✓	✓
5WG1221-2DB13	KNX Taster 1-fach, i-system, titanweiß, LED	KNX Wall switch, single, i-system, titanium white, LED	✓	✓	✓	✓	✓
5WG1222-2DB12	KNX Taster 2-fach, i-system, titanweiß	KNX Wall switch, double, i-system, titanium white	✓	✓	✓	✓	✓

5WG1222-2DB13	KNX Taster 2-fach, i-system, titanweiß, LED	KNX Wall switch, double, i-system, titanium white, LED	✓	✓	✓	✓	✓
5WG1223-2AB14	KNX Taster 3-fach, i-system, titanweiß, LED	KNX Wall switch, triple, i-system, titanium white, LED	✓	✓	✓	✓	✓
5WG1223-2DB12	KNX Taster 3-fach, i-system, titanweiß	KNX Wall switch, triple, i-system, titanium white	✓	✓	✓	✓	✓
5WG1223-2DB13	KNX Taster 3-fach, i-system, titanweiß, LED	KNX Wall switch, triple, i-system, titanium white, LED	✓	✓	✓	✓	✓
5WG1227-2AB11	KNX Raumbediengerät, Display, kapazitive Tasten	KNX Room control unit, capacitive buttons	✓	✓	✓	✓	✓
5WG1251-2AB11	KNX Bewegungsmelder WALL	KNX Motion detector WALL	✓	✓	✓	✓	✓
5WG1251-2AB12	KNX Bewegungsmelder WALL schwarz	KNX Motion detector WALL black	✓	✓	✓	✓	✓
5WG1255-2DB21	KNX Helligkeitssensor/-regler	KNX brightness sensor / controller	✓	✓	✓	✓	✓
5WG1258-2DB12	KNX Präsenzmelder DESK, Helligkeitssensor	KNX Presence detector DESK, brightness sensor	✓	✓	✓	✓	✓
5WG1258-2DB31	KNX Präsenzmelder WIDE	KNX Presence Detector WIDE	✓	✓	✓	✓	✓
5WG1258-2DB33	KNX Präsenzmelder WIDE schwarz	KNX Presence Detector WIDE black	✓	✓	✓	✓	✓
5WG1258-2DB41	KNX Präsenzmelder WIDE pro	KNX Presence Detector WIDE pro	✓	✓	✓	✓	✓
5WG1258-2DB43	KNX Präsenzmelder WIDE pro, schwarz	KNX Presence Detector WIDE pro, black	✓	✓	✓	✓	✓
5WG1258-2DB51	KNX Präsenzmelder WIDE multi	KNX Presence Detector WIDE multi	✓	✓	✓	✓	✓
5WG1258-2DB53	KNX Präsenzmelder WIDE multi, schwarz	KNX Presence Detector WIDE multi, black	✓	✓	✓	✓	✓
5WG1258-2DB61	KNX Präsenzmelder WIDE DualTech	KNX Presence Detector WIDE DualTech	✓	✓	✓	✓	✓
5WG1258-2EB22	KNX Präsenzmelder DESK, Konstantlichtregler	KNX Presence detector DESK, constant light level control	✓	✓	✓	✓	✓
5WG1260-4AB23	KNX Binäreingang, 4x AC/DC 12-230 V, RS	KNX Binary inputs, 4x AC/DC 12-230 V, RS	✓	✓	✓	✓	✓
5WG1260-4CB23	KNX Binäreingang, 4x AC/DC 12 - 230 V, UL	KNX Binary input, 4x AC/DC 12 - 230 V, UL	✓	✓	✓	✓	✓
5WG1262-1DB31	KNX Binäreingang, 4x potentialfrei	KNX Binary inputs, 4 x dry contacts	✓	✓	✓	✓	✓
5WG1262-1DB51	KNX Binäreingang, 8x potentialfrei	KNX Binary inputs, 8 x dry contacts	✓	✓	✓	✓	✓
5WG1263-1DB31	KNX Binäreingang, 4x 10 - 230 V	KNX Binary inputs, 4 x 10 - 230 V	✓	✓	✓	✓	✓
5WG1263-1DB51	KNX Binäreingang, 8x 10 - 230 V	KNX Binary inputs, 8 x 10 - 230 V	✓	✓	✓	✓	✓
5WG1285-2DB12	KNX Taster 1-fach, DELTA style, titanweiß	KNX Wall switch, single, DELTA style, titanium white	✓	✓	✓	✓	✓
5WG1285-2DB13	KNX Taster 1-fach, DELTA style, titanweiß, LED	KNX Wall switch, single, DELTA style, titanium white, LED	✓	✓	✓	✓	✓
5WG1286-2DB12	KNX Taster 2-fach, DELTA style, titanweiß	KNX Wall switch, double, DELTA style, titanium white	✓	✓	✓	✓	✓
5WG1286-2DB13	KNX Taster 2-fach, DELTA style, titanweiß, LED	KNX Wall switch, double, DELTA style, titanium white, LED	✓	✓	✓	✓	✓
5WG1287-2AB14	KNX Taster 4-fach, DELTA style, titanweiß, LED	KNX Wall switch, quadruple, DELTA style, titanium white, LED	✓	✓	✓	✓	✓
5WG1287-2DB12	KNX Taster 4-fach, DELTA style, titanweiß	KNX Wall switch, quadruple, DELTA style, titanium white	✓	✓	✓	✓	✓
5WG1287-2DB13	KNX Taster 4-fach, DELTA style, titanweiß, LED	KNX Wall switch, quadruple, DELTA style, titanium white, LED	✓	✓	✓	✓	✓
5WG1510-2AB03	KNX Binärausgang 2x 10A, AC 230 V, BTM-Schnittstelle	KNX Binary outputs, 2x 10A, AC 230 V, BTM interface	✓	✓	✓	✓	✓

5WG1510-2AB13	KNX Binärausgang, 2x 10A, AC 230 V	KNX Binary outputs, 2x 10A, AC 230 V	✓	✓	✓	✓	✓
5WG1510-2AB23	KNX Binärausgang, 2x 10A, AC 230 V, RS	KNX Binary outputs, 2x 10A, AC 230 V, RS	✓	✓	✓	✓	✓
5WG1510-2KB23	KNX Thermoantriebsaktor, 2x 1.5A, AC 24 - 230 V, DC 24 V	KNX Thermal drive actuator, 2x 1.5A, AC 24 - 230 V, DC 24 V	✓	✓	✓	✓	✓
5WG1510-4CB23	KNX Binärausgang, 2x AC 277 V, 8 A, UL	KNX Binary output, 2x AC 277 V, 8 A, UL	✓	✓	✓	✓	✓
5WG1511-2SB32	KNX Schaltaktor, 1x 16A, secure	KNX Switch actuator, 1x 16 A, secure	✗	✓	✗	✗	✗
5WG1512-1CB01	KNX Lastschalter 8x AC 277/347 V, 20 A, UL	KNX Switch actuator, 8x AC 277/347 V 20 A, UL	✓	✓	✓	✓	✓
5WG1512-4AB23	KNX Schaltaktor 1x AC 230 V, 16 A	KNX Switch actuator, 1x AC 230 V, 16 A	✓	✓	✓	✓	✓
5WG1512-4CB23	KNX Schaltaktor, 1x AC 277/347 V, 20 A, UL	KNX Switch actuator, 1x AC 277/347 V, 20 A, UL	✓	✓	✓	✓	✓
5WG1513-4CB23	KNX Binärausgang, 3x AC 277 V, 6 A, UL	KNX Binary output, 3x AC 277 V, 6 A, UL	✓	✓	✓	✓	✓
5WG1513-4DB23	KNX Binärausgang, 3x AC 230 V, 6 A	KNX Binary output, 3x AC 230 V, 6 A,	✓	✓	✓	✓	✓
5WG1520-2AB03	KNX Jalousieaktor, 1x AC 230 V, 6A, BTM-Schnittstelle	KNX Blind actuator, 1x AC 230 V, 6A, BTM interface	✓	✓	✓	✓	✓
5WG1520-2AB13	KNX Jalousieaktor, 1x AC 230 V, 6A	KNX Blind actuator, 1x AC 230 V, 6A	✓	✓	✓	✓	✓
5WG1520-2AB23	KNX Jalousieaktor, 1x AC 230 V, 6A, RS	KNX Blind actuator, 1x AC 230 V, 6A, RS	✓	✓	✓	✓	✓
5WG1520-4CB23	KNX Jalousieaktor, 1x AC 120 V, 6A, UL	KNX Blind actuator, 1x AC 120 V, 6A, UL	✓	✓	✓	✓	✓
5WG1521-4AB23	KNX Jalousieaktor, 2x AC 230 V, 6 A	KNX Blind actuator, 2x AC 230 V, 6 A, RS	✓	✓	✓	✓	✓
5WG1521-4CB23	KNX Jalousieaktor, 2x AC 120 V, 6 A, UL	KNX Blinds actuator, 2x AC 120 V, 6 A, UL	✓	✓	✓	✓	✓
5WG1524-4DB23	KNX Sonnenschutzaktor, 2x DC 24 V, 6 A	KNX Solar protection actuator, 2x DC 24 V, 6 A	✓	✓	✓	✓	✓
5WG1525-1DB11	KNX Schalt-/Dimmaktor, 2x DALI, Broadcast	KNX Switch/dim actuator, 2x DALI, broadcast	✓	✓	✓	✓	✓
5WG1525-2AB03	KNX Universaldimmer, 1x 250 VA, AC 230 V	KNX Universal dimmer, 1x 250 VA, AC 230 V, BTM interface	✓	✓	✓	✓	✓
5WG1525-2AB13	KNX Universaldimmer, 1x 250 VA, AC 230 V	KNX Universal dimmer, 1x 250 VA, AC 230 V	✓	✓	✓	✓	✓
5WG1525-2AB23	KNX Universaldimmer, 1x 250 VA, AC 230 V, RS	KNX Universal dimmer, 1x 250 VA, AC 230 V, RS	✓	✓	✓	✓	✓
5WG1525-2SB32	KNX Universaldimmer, 1x AC 230 V, LED, secure	KNX Universal dimmer, 1x AC 230 V, LED, secure	✗	✓	✗	✗	✗
5WG1525-4CB23	KNX Universaldimmer, 1x 125 VA, AC 120 V, UL	KNX Universal dimmer, 1x 125 VA, AC 120 V, UL	✓	✓	✓	✓	✓
5WG1526-4CB23	KNX Schalt-/Dimmaktor, 2x AC 277 V, 20A, 1...10 V, UL	KNX Switch/dim actuator, 2x AC 277 V, 20A, 1...10 V, UL	✓	✓	✓	✓	✓
5WG1526-4DB23	KNX Schalt-/Dimmaktor, 2x AC 230 V, 6 A, 1...10 V	KNX Switch/dim actuator, 2x AC 230 V, 6 A, 1...10 V	✓	✓	✓	✓	✓
5WG1527-4CB23	KNX Schalt-/Dimmaktor, 1x AC 277 V, 20A, 1...10 V, UL	KNX Switch/dim actuator, 1x AC 277 V, 20A, 1...10 V, UL	✓	✓	✓	✓	✓
5WG1528-1CB01	KNX Universaldimmer 2x 150 VA, AC 120 V, LED, UL	KNX Universal dimmer, 2x 150 VA, AC 120 V, LED, UL	✓	✓	✓	✓	✓
5WG1528-1DB01	KNX Universaldimmer 2x 300 VA, AC 230 V, LED	KNX Universal dimmer, 2x 300VA, AC 230 V, LED	✓	✓	✓	✓	✓
5WG1530-1DB31	KNX Schaltaktor, 4x AC 230 V, 6 AX	KNX Switch actuator, 4x AC 230 V, 6 AX	✓	✓	✓	✓	✓
5WG1530-1DB51	KNX Schaltaktor, 8x AC 230 V, 6 AX	KNX Switch actuator, 8x AC 230 V, 6 AX	✓	✓	✓	✓	✓
5WG1530-1DB61	KNX Schaltaktor, 12x AC 230 V, 6 AX	KNX Switch actuator, 12x AC 230 V, 6 AX	✓	✓	✓	✓	✓

5WG1532-1DB31	KNX Schaltaktor, 4x AC 230 V, 10 AX, 16 A AC1	KNX Switch actuator, 4x AC 230 V, 10 AX, 16 A AC1	✓	✓	✓	✓	✓
5WG1532-1DB51	KNX Schaltaktor, 8x AC 230 V, 10 AX, 16 A AC1	KNX Switch actuator, 8x AC 230 V, 10 AX, 16 A AC1	✓	✓	✓	✓	✓
5WG1532-1DB61	KNX Schaltaktor, 12x AC 230 V, 10 AX, 16 A AC1	KNX Switch actuator, 12x AC 230 V, 10 AX, 16 A AC1	✓	✓	✓	✓	✓
5WG1534-1DB31	KNX Schaltaktor, 4x AC 230 V, 16/20 AX	KNX Switch actuator, 4x AC 230 V, 16/20 AX	✓	✓	✓	✓	✓
5WG1534-1DB51	KNX Schaltaktor, 8x AC 230 V, 16/20 AX	KNX Switch actuator, 8x AC 230 V, 16/20 AX	✓	✓	✓	✓	✓
5WG1534-1DB61	KNX Schaltaktor, 16x AC 230 V, 16/20 AX	KNX Switch actuator, 12x AC 230 V, 16/20 AX	✓	✓	✓	✓	✓
5WG1535-1DB31	KNX Schaltaktor, 4x AC 230 V, 16/20 AX, Last-Check	KNX Switch actuator, 4x AC 230 V, 16/20 AX, load check	✓	✓	✓	✓	✓
5WG1535-1DB51	KNX Schaltaktor, 8x AC 230 V, 16/20 AX, Last-Check	KNX Switch actuator, 8x AC 230 V, 16/20 AX, load check	✓	✓	✓	✓	✓
5WG1535-1DB61	KNX Schaltaktor, 12x AC 230 V, 16/20 AX, Last-Check	KNX Switch actuator, 12x AC 230 V, 16/20 AX, load check	✓	✓	✓	✓	✓
5WG1536-1DB31	KNX Schalt-/Dimmaktor, 4x AC 230 V, 10 AX, 1...10 V	KNX Switch/dim actuator, 4x AC 230 V, 10 AX, 1...10 V	✓	✓	✓	✓	✓
5WG1536-1DB51	KNX Schalt-/Dimmaktor, 8x AC 230 V, 10 AX, 1...10 V	KNX Switch/dim actuator, 8x AC 230 V, 10 AX, 1...10 V	✓	✓	✓	✓	✓
5WG1543-1DB31	KNX Sonnenschutzaktor, 4x AC 230 V, 6A	KNX Solar protection actuator, 4x AC 230 V, 6A	✓	✓	✓	✓	✓
5WG1543-1DB51	KNX Sonnenschutzaktor, 8x AC 230 V, 6A	KNX Solar protection actuator, 8x AC 230 V, 6A	✓	✓	✓	✓	✓
5WG1545-1DB31	KNX Sonnenschutzaktor, 4x DC 24 V, 6 A	KNX Solar protection actuator, 4x DC 24 V, 6 A	✓	✓	✓	✓	✓
5WG1554-1DB31	KNX Universaldimmer, 4x 300 VA / 1x 1000 VA, AC 230 V	KNX Universal dimmer, 4x 300VA, 1x 1000VA, AC 230 V	✓	✓	✓	✓	✓
5WG1562-2SB32	KNX Schalt-/Sonnenschutzaktor, 2x AC 230 V, 6 A	KNX Switch/solar protection actuator, 2x AC 230 V, 6A	✗	✓	✗	✗	✗
5WG1568-1AB81	KNX Multi-Raumaktor, 24-fach	KNX Multi room actuator, 24-fold	✓	✓	✗	✗	✗
5WG1605-1DB41	KNX Thermoantriebsaktor, 6 x AC 24 - 230 V, T-Regler	KNX Thermal drive actuator, 6 x AC 24 - 230 V, t controller	✓	✓	✓	✓	✓
5WG1605-4DB23	KNX Thermoantriebsaktor, 2 x AC 24 - 230 V, T-Regler	KNX Thermal drive actuator, 2 x AC 24 - 230 V, t controller	✓	✓	✓	✓	✓
S55720-S604	KNX Raumfühler QMX6.P30, Temp., weiß	KNX Room sensor QMX6.P30, temp., white	✓	✓	✗	✗	✗
S55720-S605	KNX Raumfühler QMX6.P40, Temp., Feuchte, weiß	KNX Room sensor QMX6.P40, temp., rel. humidity, white	✓	✓	✗	✗	✗
S55720-S606	KNX Raumfühler QMX6.P70, Temp., Feuchte, CO2, weiß	KNX Room sensor QMX6.P70, temp., rel. humidity, CO2, white	✓	✓	✗	✗	✗
S55720-S607	KNX Raumbediengerät QMX6.P34, Temp., weiß	KNX Room unit QMX6.P34, temp, white	✓	✓	✗	✗	✗
S55720-S608	KNX Raumbediengerät QMX6.P44, Temp., Feuchte, weiß	KNX Room unit QMX6.P44, temp., rel. humidity, white	✓	✓	✗	✗	✗
S55720-S609	KNX Raumbediengerät QMX6.P74, Temp., rel. F., CO2, weiß	KNX Room unit QMX6.P70, temp., rel. humidity, CO2, white	✓	✓	✗	✗	✗
S55720-S642	KNX Raumfühler QMX6.P30, Temp., schwarz	KNX Room sensor QMX6.P30, temp., black	✓	✓	✗	✗	✗
S55720-S643	KNX Raumfühler QMX6.P40, Temp., Feuchte, schwarz	KNX Room sensor QMX6.P40, temp., rel. humidity, black	✓	✓	✗	✗	✗
S55720-S644	KNX Raumfühler QMX6.P70, Temp., Feuchte, CO2, schwarz	KNX Room sensor QMX6.P70, temp., rel. humidity, CO2, black	✓	✓	✗	✗	✗
S55720-S645	KNX Raumbediengerät QMX6.P34, Temp., schwarz	KNX Room unit QMX6.P34, temp, black	✓	✓	✗	✗	✗
S55720-S656	KNX Raumbediengerät QMX6.P44, Temp., Feuchte, schwarz	KNX Room unit QMX6.P44, temp., rel. humidity, black	✓	✓	✗	✗	✗
S55720-S567	KNX Raumbediengerät QMX6.P74, Temp., rel. F., CO2, sw.	KNX Room unit QMX6.P70, temp., rel. humidity, CO2, black	✓	✓	✗	✗	✗

S55624-H103	Wandmontage-Raumtemperaturfühler	Wall-mounted room temperature sensor	✓	✓	✓	✓	✓
S55624-H104	Wandmontage-Raummehr-fachfühler Luftqualitäts-LED	Wall-mounted room multi sensor and air quality-LED	✓	✓	✓	✓	✓
S55624-H106	Wandmontage-Raumbedien-gerät mit LCD Display	Wall-mounted room operating unit with LCD display	✓	✓	✓	✓	✓
S55770-T293	RDF600KN KNX Raumregler	RDF600KN KNX room controller	✓	✓	✓	✓	✓
S55770-T350	RDF800KN Raumtemperaturregler	RDF800KN KNX room temp controller	✓	✓	✓	✓	✓
S55770-T400	RDF600KN/S KNX Raumregler	RDF600KN/S KNX room controller	✓	✓	✓	✓	✓
S55770-T348	Raumthermostat	Room Thermostat	✓	✓	✓	✓	✓
S55770-T407	RDF870KN PM2.5 & CO2 Regler KNX	RDF870KN PM2.5 & CO2 Controller KNX	✓	✓	✓	✓	✓
S55770-T409	Raumthermostat RDG200KN Fan coil	Wall-mounted room thermostat RDG200KN, for fan coil	✓	✓	✓	✓	✓
S55770-T410	Raumthermostat RDG204KN Fan coil	Wall-mounted room thermostat RDG204KN, for fan coil	✓	✓	✓	✓	✓
S55770-T412	Raumthermostat RDG260KN Fan coil	Wall-mounted room thermostat RDG260KN, for fan coil	✓	✓	✓	✓	✓
S55770-T413	Raumthermostat RDG264KN Fan coil	Wall-mounted room thermostat RDG264KN, for fan coil	✓	✓	✓	✓	✓
S55770-T429	RDF800KN/VB Raumthermostat Schwarz	RDF800KN/VB Room Thermostat Black	✓	✓	✓	✓	✓
S55770-T430	RDF600KN/VB Raumthermostat Schwarz	RDF600KN/VB Room Thermostat Black	✓	✓	✓	✓	✓
S55770-T452	Raumthermostat RDG200KN/BK Fan coil	Room thermostat RDG200KN/BK, for fan coil	✓	✓	✓	✓	✓
S55770-T453	Raumthermostat RDG260KN/BK, schwarz	Room thermostat RDG260KN/BK black	✓	✓	✓	✓	✓
S55720-S203	AQR2570NF Unterputzfühler BASI	AQR2570NF flush-mounted sensor module	✓	✓	✓	✓	✓
S55720-S207	AQR2576NF Unterputzfühler Basismodul CO2 Dual KNX	AQR2576NF Flush-mounted sensor base module CO2	✓	✓	✓	✓	✓
S55370-C162	Steuerzentrale	Central control unit	✓	✗	✗	✗	✗
BPZ:RMU710B-1	modularer Universalregler SYNCO für KNX RMU	RMU710B-1 Universal Contr, 1 Contr Loop	✓	✗	✗	✗	✗
BPZ:RMU720B-1	modularer Universalregler SYNCO für KNX	Universal controller 2 control loop	✓	✗	✗	✗	✗
BPZ:RMU730B-1	modularer Universalregler SYNCO für KNX	Universal controller 3 control loop	✓	✗	✗	✗	✗
S55370-C100	Steuerungs- und Überwachungsgerät	Switching and monitoring device	✓	✗	✗	✗	✗
BPZ:RMH760B-1	MOD Heizungsregler	RMH760B-1Heating Controller	✓	✗	✗	✗	✗
BPZ:RMK770-1	Kesselfolge-Manager	RMK770-1Boiler Sequence Controller	✓	✗	✗	✗	✗
S55180-A111	Ventilantrieb 100N	Valve Actuator 100N	✓	✓	✗	✗	✗
S55499-D134	Stellantrieb VAV KNX, AC 24 V, 5 Nm, NSR	Damper actuator VAV KNX, AC 24 V, 5 Nm, NSR	✓	✗	✓	✗	✓
S55499-D505	GDB181.1EMKN VAV KNX Multipack 18 Stk.	GDB181.1EMKN VAV KNX Multipack 18 pcs.	✓	✗	✓	✗	✓
S55499-D190	Luftklappenantrieb, busfähig, AC24V, 5 Nm, NSR, KNX	Damper actuator, Bus capable, AC24V, 5 Nm, NSR, KNX	✓	✗	✓	✗	✓
S55499-D203	Drehantrieb für Kugelventil, busfähig, AC24V, 5 Nm, NSR	Actuator for ball valve, Bus capable, AC24V, 5 Nm, NSR	✓	✗	✓	✗	✓
S55499-D135	Stellantrieb VAV KNX, AC 24 V, 10 Nm, NSR	Damper actuator VAV KNX, AC 24 V, 10 Nm, NSR	✓	✗	✓	✗	✓

<b>S55499-D263</b>	Stellantrieb VAV KNX, AC 24 V, 10 Nm	Damper actuator VAV KNX, AC 24 V, 10 Nm	✓	✗	✓	✗	✓
<b>S55499-D198</b>	Luftklappenantrieb, busfähig, AC24V, 10 Nm, NSR, KNX	Damper actuator, Bus capable, AC24V, 10 Nm, NSR, KNX	✓	✗	✓	✗	✓
<b>S55499-D207</b>	Drehantrieb für Kugelventil, busfähig, AC24V, 10 Nm, NSR	Actuator for ball valve, Bus capable, AC24V, 10 Nm, NSR	✓	✗	✓	✗	✓
<b>BPZ:QAW740</b>	Raumgerät SYNCO mit KONNEX-Schnittstelle	QAW740 room unit with KONNEX interface	✓	✗	✗	✗	✗

## Product documentation

Zugehörige Dokumente wie technische Produktinformationen, Bedien-/Montageanleitung, Applikationsbeschreibung, Produktdatenbank, Zusatzsoftware, Produktbild, CE-Deklarationen u. a. können unter nachstehender Internet-Adresse heruntergeladen werden




Associated documents such as the technical product information, operating and installation instructions, application program description, product database, additional software, product image, CE declaration etc. can be downloaded from the following internet address:



<http://www.siemens.com/gamma-td>

## Support

- Bereitstellung von Bedien-/Montageanleitungen
- Ein defektes Gerät mit einem Rücklieferschein an die zuständige Vertriebsniederlassung zurücksenden.
- Kontaktdaten des Technical Supports für zusätzliche Fragen zum Produkt:
- Provision of operating/installation instructions
- Return a defective device to the appropriate sales office.
- Contact details for technical support in case of additional questions relating to the product:

 +49 911 895-7222  
 +49 911 895-7223  
 [support.automation@siemens.com](mailto:support.automation@siemens.com)  
<http://www.siemens.com/supportrequest>



Technical Support:  
<http://www.siemens.com/supportrequest>



FAQ:  
<https://support.industry.siemens.com/cs/ww/en/ps/faq>

---

<sup>1</sup> MLFB = Maschinenlesbare Fabrikatsbezeichnung/Machine readable product name  
<sup>2</sup> ASN = Article Serial Number